

## General Information

|                        |                                                                                                                                           |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type: | 363RS6W                                                                                                                                   |
| Product ID:            | 2CMA167316R1000                                                                                                                           |
| EAN:                   | 7392696673167                                                                                                                             |
| Catalog Description:   | Surface socket-outlet, 6h, 63A, IP67, 3P+E                                                                                                |
| Long Description:      | Surface socket-outlet, earthing sleeve position 6h, rated current 63A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red |

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

## Ordering

|                         |                     |
|-------------------------|---------------------|
| EAN:                    | 7392696673167       |
| Minimum Order Quantity: | 1 piece             |
| Country of Origin:      | Czech Republic (CZ) |

## Dimensions

|                     |         |
|---------------------|---------|
| Product Net Width:  | 118 mm  |
| Product Net Height: | 263 mm  |
| Product Net Length: | 150 mm  |
| Product Net Depth:  | 263 mm  |
| Product Net Weight: | 1.07 kg |

## Container Information

|                               |               |
|-------------------------------|---------------|
| Package Level 1 Width:        | 124 mm        |
| Package Level 1 Length:       | 337 mm        |
| Package Level 1 Height:       | 153 mm        |
| Package Level 1 Gross Weight: | 1.18 kg       |
| Package Level 1 EAN:          | 7392696673167 |
| Package Level 1 Units:        | 1 piece       |

## Environmental

|              |                                                                                          |
|--------------|------------------------------------------------------------------------------------------|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01 |
|--------------|------------------------------------------------------------------------------------------|

## Certificates and Declarations (Document Number)

|                                 |                 |
|---------------------------------|-----------------|
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Environmental Information:      | 2CMC700001D0002 |
| RoHS Information:               | 2CMC700057D0001 |

## Additional Information

|                                  |                               |
|----------------------------------|-------------------------------|
| Additional Information:          | Cable entry Ø32mm             |
| Cable Cross-Section:             | 6 ... 25 mm²                  |
| Color:                           | Red                           |
| Degree of Protection:            | acc. to IEC 60529 IP67        |
| Enclosure Material:              | Thermoplastic polyester (PBT) |
| Frequency (f):                   | 50 Hz<br>60 Hz                |
| Function:                        | Surface socket outlet         |
| IIT Publishing Status:           | Level 0 - Information enabled |
| Invoice Description:             | Ind. P&S#363RS6W              |
| Number of Poles:                 | 4                             |
| Object Classification Code:      | 2CMT005069                    |
| Product Main Type:               | RS                            |
| Product Name:                    | Industrial Socket Outlet      |
| Protection Type:                 | Watertight                    |
| Rated Current (I <sub>n</sub> ): | 63 A                          |
| Rated Voltage (U <sub>r</sub> ): | 380 ... 415 V                 |
| RoHS Date:                       | L23                           |
| Standards:                       | IEC 60309-1,-2                |
| Suitable For:                    | Surface Socket Outlets        |

|                             |                              |
|-----------------------------|------------------------------|
| Suitable for Product Class: | Industrial Plugs and Sockets |
|-----------------------------|------------------------------|

## Classifications

|           |          |
|-----------|----------|
| E-nummer: | 2416575  |
| UNSPSC:   | 39120000 |

