

5360 9230	2 x 3.0	9	100
5361 1330	3 x 3.0	11	100
5361 1240	2 x 4.0	11	100
5361 3250	2 x 5.0	13	100
5361 3340	3 x 4.0	13	100
5361 6340	3 x 4.0	16	50
5361 6540	5 x 4.0	16	50
5361 6450	4 x 5.0	16	50
5361 6356	3 x 5.6	16	50
5361 6260	2 x 6.0	16	50
5361 6360	3 x 6.0	16	50
5362 1460	4 x 6.0	21	50
5362 1370	3 x 7.0	21	50
5362 1280	2 x 8.0	21	50
5362 9470	4 x 7.0	29	50
5362 9490	4 x 9.0	29	50



[back to top](#)

Please click below to choose another gland from this section:

NYLON CABLE GLANDS

[SKINTOP® PG, ISO metric, ST-M](#)

[SKINTOP® B - for Strain Relief](#)

[SKINTOP® ST, STR, BS & STE](#)

[SKINTOP® BT](#)

[SKINTOP® K-M, KR-M ATEX](#)

[SKINTOP® KR1-M ATEX](#)

[SKINTOP® K-M, KR-M ATEX Blue](#)

[SKINTOP® KR1-M ATEX Blue](#)

[SKINTOP® Accessories](#)

BRASS CABLE GLANDS

[SKINTOP® MS-SC - EMC Gland](#)

[SKINTOP® MS](#)

[SKINTOP® MSR](#)

[SKINDICHT® MSE](#)

[SKINDICHT® SHZ](#)

[SKINTOP® MS-EX EExe II-C-Generation](#)

[SKINDICHT® SVF - for Flat cable](#)

[SKINDICHT® SVRE](#)

[SKINDICHT® SKZ - for Braided cable](#)

[SKINDICHT® SHV](#)

[SKINTOP® SHV-Viton](#)

- for high temperatures

[SKINDICHT® SHVE](#)

[SKINDICHT® SR - for Strain Relief](#)

[SKINDICHT® SR-SV - for high temperatures](#)

[SKINDICHT® SRE - Strain Relief for braided cable](#)

[SKINDICHT® SR-SVE - for high temperatures](#)

[E1XF - for high temperatures](#)

[A2F - Flameproof brass glands](#)

[CX - for braided cable](#)

[A2](#)

BRASS GLAND COMPONENTS:

[SKINDICHT® ME & MR, SKINDICHT® SM & BL](#)

[SKINDICHT® ZS-i Converters, SKINDICHT® EH](#)

Or click below if you wish to go to the next section or return to products contents page:

[next section](#) | [return to product contents page](#)
(Cable Accessories)

HOLE PLUGS

Brass and Plastic for use in PG and Metric Threaded Holes



Hole Plugs (BL)



Technical Data:



Materials: Nickel-Plated Brass

Brass hole plugs are for use when existing PG-threaded holes are not yet, or no longer required.

Part Number	Thread Type & Size	Standard Pack Size
52002680	PG-7	100
52003390	PG-9	100
52003400	PG-11	100
52003410	PG-13	100
52003420	PG-16	100
52003430	PG-21	50
52003440	PG-29	50
52003450	PG-36	25
52003460	PG-42	10
52002790	PG-48	10

Hole Plugs (BL-M)



Technical Data:



Materials: Nickel-Plated Brass

Brass hole plugs are used when existing Metric-threaded holes are not yet, or no longer required.

Part Number	Thread Type & Size	Standard Pack Size
52103100	M-12X1.5	100
52103110	M-16X1.5	100
52103120	M-20X1.5	100
52103130	M-25X1.5	100
52103140	M-32X1.5	50
52103150	M-40X1.5	50
52103160	M-50X1.5	25
52103170	M-63X1.5	25

Hole Plugs (BLK)



Technical Data:



Materials: Gray Polystyrene

BLK Plastic hole plugs are for use when existing PG-threaded holes are not yet, or no longer required.

Part Number	Thread Type & Size	Standard Pack Size
52005949	PG-7	100
52005950	PG-9	100
52005960	PG-11	100
52005970	PG-13	100
52005980	PG-16	100
52005990	PG-21	50
52006000	PG-29	50
52006010	PG-36	25
52006020	PG-42	25
52006030	PG-48	25

Hole Plugs (BLK-GL-M)



Technical Data:



Materials: Gray Polystyrene

BLK-GL-M Plastic hole plugs are for use when existing Metric-threaded holes are not yet, or no longer required.

Part Number	Thread Type & Size	Standard Pack Size
52006100	M-12X1.5	100
52006110	M-16X1.5	100
52006120	M-20X1.5	100
52006130	M-25X1.5	100
52006140	M-32X1.5	50
52006150	M-40X1.5	25
52006160	M-50X1.5	25
52006170	M-63X1.5	25