

Socket insert - VS-SI-SD-GB - 1656547

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Ground contact socket, exclusively for service interface order no. 1656482 and 1656495, plastic, for Great Britain



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	74.9 g
Custom tariff number	85366990
Country of origin	Czech Republic

Technical data

Mechanical characteristics

Connection method	Screw connection
Conductor cross section	2.5 mm ²
Connection cross section AWG	14
Color	gray

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Degree of protection	IP20

Material data

Flammability rating according to UL 94	V0
Housing material	PA

Electrical characteristics

Rated voltage (III/3)	250 V
Rated current	13 A

Socket insert - VS-SI-SD-GB - 1656547

Classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27142305

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC000125
ETIM 4.0	EC000125
ETIM 5.0	EC001663

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Socket insert - VS-SI-SD-GB - 1656547

Drawings

Dimensional
drawing

Socket
insert

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>