






LOC	QTY	REV	DATE	BY	APPV
CM	53				
REVISIONS					
REV	DESCRIPTION	DATE	BY	APPV	
E	REV & REDWN PER EC 0L30-0241-97	11-04-97	KW	RS	


- 1

AMP LOGO AND CIRCUIT ID NUMBERS LOCATED ON THIS SURFACE.
- 2

OPPOSITE SIDE OPTIONAL.



RECOMMENDED CUT OUT
FOR 1.58 MAX THICK PANEL



3-DIMENSIONAL MODEL
NTS

6.35	.250	32.51	1.280
1.58	.062	28.96	1.140
0.64	.025	23.37	.920
0.38	.015	19.43	.765
0.25	.010	7.87	.310
0.13	.005	6.48	.255
MM	IN	MM	IN
CONVERSION TABLE			

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

UNLESS

#-

#-

±0.13

#-

#-

#-

MATERIAL

NYLON,
UL 94V-2,NATURAL

FINISH

-

DWN

K. WHITAKER

11-04-97

CHK

R. SWING

11-04-97

APVD

K. CORLE

11-04-97

PRODUCT SPEC

-

APPLICATION SPEC

-

HEIGHT

-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

RECEPTACLE,
PANEL MOUNT,3 CIRCUIT,
.250 PIN AND SOCKET

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

770269

-

SCALE

4:1

SHEET

1

OF

1

REV

F