

Datasheet

DIN Connector Sockets, ME - 211/SL-*

RS Stock number 811-8301



Specifications:

Connection Type:

2 Pole + Earth

Voltage:

12 VDC / 24 VDC / 48 VDC / 110 VDC /
250 VDC / 110 VAC / 250 VAC

Approvals:

N.A.

Standard:

N.A.

Mounting:

Screw-type

Type:

ME-Socket - Illuminated

Socket Type:

Type A

DC V Range:

12,24, 48

Mounting:

M3 Screw

Material For Rubber Gasket:

Nitril / Silicon

Material Body:

Polycarbonate

Gland Size:

PG-11

Body Colours:

Transparent Body

Contact Resistance (Initial):

20 m Ohms max. (Initial)

Current Carrying Parts:

Copper Alloy, Tin plated

Permissible Temp. With/Without Load:

0°C to 90°C

Rating:

10A 110VAC, 230VAC

Terminals:

Screw-type

H. V. Breakdown Test:

2KV AC For 1 Minute .

Insulation Resistance:

100 M Ohms min.

Unit mm

