







NOTES:

1. MATERIAL: NYLON TYPE 6/6, 94V-2.
2. FINISH: NONE
3. PRODUCT SPECIFICATION: PS-02-06
4. PACKAGING INFORMATION: PK-1625-001
5. THIS HOUSING FOR USE WITH .062/(1.57) DIA. TERMINALS.

△ WHERE DENOTED IN CHART, TOOLS ARE BUILT WITH PREBENT MOUNTING EARS PER DETAIL 2 AND SUPERSEDE ALL TOOLS PREVIOUSLY BUILT WITH THE STANDARD MOUNTING EARS.

△ CIRCUIT ID. NUMBERS APPEAR ON PARTS FROM TOOLS BUILT AFTER 2/1/93.

RECEP.	.795 (20.19)	.563 (14.30)		.23 (5.8)
PLUG	.903 (22.94)	.614 (15.60)	.21 (5.3)	.22 (5.5)
PART	DIM. A	DIM. B	DIM. C (STANDARD EAR)	DIM. C (PREBENT EAR)

TRANSLATED TO SD. EC NO: UCP2004-2551 DRAWN: RHOLTS 2004/12/03 CHKD: FSMTH 2004/12/03 APPR: FSMTH 2004/12/06	DESCRIPTION REV	QUALITY SYMBOLS ▽ - 0 ◻ - 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			SCALE 1:1	DESIGN UNITS INCH			THIRD ANGLE PROJECTION	REVISE ON CAD ONLY	
				mm	INCH	DIMENSION STYLE IN/MM						TITLE .062/(1.57) HOUSINGS, PLUG & RECEPTACLE 12 CKT, 145 CENTERS MOLEX MOLEX INCORPORATED
			4 PLACES	± ---	± ---	DRAWN BY GWC	DATE 1993/02/01	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-1625-12*	SHEET NO. 2 OF 2		
			3 PLACES	± ---	± .010	CHECKED BY RW	DATE 1993/02/01					
			2 PLACES	± 0.25	± .014							
			1 PLACE	± 0.36	± ---	APPROVED BY RAS	DATE 1993/02/01					
			ANGULAR ± 1 °			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			DRAFT WHERE APPLICABLE									
			MUST REMAIN WITHIN DIMENSIONS									