

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [26-03-4121](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK® 3.96mm Crimp Terminal Housing, Use With Trifurcon® Terminals, Friction Ramp, 12 Circuits](#)

**Documents:**

[3D Model](#) [Product Specification PS-40-02 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR19980

**General**

Product Family Crimp Housings  
 Series [6442](#)  
 Application Power, Wire-to-Board  
 Overview [KK® Interconnect System - Molex](#)  
 Product Name KK® 396  
 UPC 800753587076

**Physical**

Circuits (maximum) 12  
 Color - Resin Natural  
 Flammability 94V-2  
 Gender Female  
 Glow-Wire Compliant No  
 Lock to Mating Part Yes  
 Material - Resin Nylon  
 Net Weight 3.192/g  
 Number of Rows 1  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 3.96mm  
 Stackable No  
 Temperature Range - Operating See Product Specification

**Material Info**

Old Part Number 6442-R12-Z

**Reference - Drawing Numbers**

Product Specification PS-40-02  
 Sales Drawing SD-6442



image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[6442Series](#)

**Mates With**

3.96mm Pitch KK® Crimp Terminal Housing  
 Use with Trifurcon® Terminals, Friction Ramp, 12 Circuits

**Use With**

[6838](#) , [7258](#) , KK® Trifurcon crimp terminals, [45570](#) MarKK™ terminal