


DO NOT SCALE

DIMENSIONS IN mm

METRIC




THIRD ANGLE

PROJECTION




NOTES

- ① SNAP-IN POLARIZERS PN. 927636-2 OR 927637-2 CAN BE APPLIED.
- ② THERE IS NO WINDOW FOR SNAP-IN POLARIZERS AT THIS END IN 10 AND 14 POS. HEADERS.
- ③ INDICATION OF FIRST POSITION.
- ④ THERE IS NO CENTER STAND-OFF IN 10-26 POS. HEADERS.
- ⑤ PARTNUMBER AND PROD.-DATE ON SUITABLE SURFACE

X-828 584-X
DD.MM.YY

RECOMMENDED PCB-HOLE PATTERN



② PIN-CONTACT

BRASS

MATING SIDE: 0,8µm AU
OR 0,8µm AMP DURAGOLD®/
OVER 1,27µm NI
SOLDER SIDE: MIN. 3,0µm SN
OVER 1,27µm NI

① HOUSING

GLASSFILLED POLYESTER

GREY

100,6	90,4	96,5	86,4	78,7	64	6-828584-4				COMPONENT NAME			MATERIAL		PLATING/COLOUR			
95,5	85,3	91,4	81,3	73,7	60	6-828584-0	-	-		-	-	-	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED					
82,8	72,6	78,7	68,6	61,0	50	5-828584-0	-	-		-	-	-	© COPYRIGHT 19- BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.					
70,1	59,9	66,0	55,9	48,3	40	4-828584-0	-	-		-	-	-	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION - ,19 -					
62,5	52,3	58,4	48,3	40,6	34	3-828584-4	-	-		-	-	-	 AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.					
52,3	42,2	48,3	38,1	30,5	26	2-828584-6	A1	PLATING DURAGOLD OR GOLD ALTERNATIVELY USABLE		MAH.	STRE.	01-JUL-03						
44,7	34,5	40,6	30,5	22,9	20	2-828584-0	A	BEMERKUNG  ERGAENZT		BLU	LAU	11.05.95	NAME					
39,6	29,5	35,6	25,4	17,8	16	1-828584-6	0	EH-0839-93		JvL	RV	29-11-93	AMP-LATCH HEADER 90° VERSION WITH LATCHES					
37,1	26,9	33,0	22,9	15,2	14	1-828584-4	LTR.	REVISION RECORD		DR.	CHK.	DATE						
32,0	21,8	27,9	17,8	10,2	10	1-828584-0												
DIM. "E"	DIM. "D"	DIM. "C"	DIM. "B"	DIM. "A"	NR. OF POSITIONS	PARTNUMBER	DR. : J.v.LIEMPT		CHK. : R.VERSTIJNEN		APP. : L.v.SOEEST		DWG.No. C-828584		LOC. AI	A3	SHEET 1 OF 1	REV.LTR. A1
VARIABLE CONNECTOR DIMENSIONS							DATE: 29-11-93		DATE: -		DATE: -							