


NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	01.18.05'
②	BACKGROUND FORMAT UPDATED	05.11.11'
③	DEL. PROOF VOLTAGE WORKING VOLTAGE → VOLTAGE RATING	05.18.15'



1.0 ELECTRICAL

1.1 FREQUENCY RANGE: DC-2.5 GHz

1.2 NOMINAL IMPEDANCE: 50 OHMS

1.3 VOLTAGE RATING: 335 VOLTS MAX. ③

2.0 MATERIALS

2.1 BODIES: BRASS PER JIS-C3604

2.2 CENTER CONTACT: BRASS PER JIS-C3604

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

4.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C

7	WASHER II	BRASS	1	NICKEL
6	INSULATION II	POM	1	NONE
5	BODY	BRASS	1	NICKEL 100μ" MIN.
4	CENTER CONTACT	BRASS	1	GOLD
3	INSULATION I	POM	1	NONE
2	WASHER I	BRASS	1	NONE
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by _____ DATE: _____



DESCRIPTION			STRAIGHT MINI-UHF PLUG-BNC JACK ADAPTER								
製圖	DRAWN	TOLERANCE		品名	12-13		D.G.N	日期	DATE	版次	REV.
	Kristina	.X	±0.2	TITLE	\ROHS COMPLIANT (50Ω)			12.24.91'		A-3	
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.		12-0041			
	Arc				mm(in)						
認定	APPROVAL	.XXX	±0.05	比例	SCALE						
	Jenny	ANGLE	±5°		4:1						