


NOTES:

1. SPECIFICATIONS:

STROKE:	3.25 IN. (82.5 mm)
LENGTH:	11.5 IN. (292 mm)
MAX. LENGTH:	15.0 IN. (381 mm)
HANDLE WIDTH:	8.0 IN. (203 mm)
WEIGHT:	4.4 LB. (2.0 kg)
MAX APPLIED STRAP TENSION:	2500 LB. (1134 kg)
MAX HANDLE FORCE:	46 LB. (20.9 kg)
COLOR:	BLUE

2. PANDUIT BT75SDT USES:

INSTALL 0.75" (19.1MM) WIDTH STRAPPING ONLY.



										CNO FILENAME/LAYERS		R26069BA_TM26069C01/01A		
										PANDUIT CORP TINLEY PARK, ILLINOIS				
										BT75SDT * CUSTOMER DRAWING				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± -- (.XXX) ± -- (.XX) ± -- ANGLES ± --		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION		
01	8-5-13	JEH	AS	UPDATED NOTES			4612	--	AS	DRAWN BY	MAT'L: -----	SCALE	NONE	
00	04-30-09	PWG	ABJ	RELEASED			4377	--	ABJ	DATE		04-30-09	DRAWING NO.	DWG
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST		SUP	OK'D	TM26069C01
										ABJ			C	