



REV	DESC	DATE	ECN NO



RoHS COMPLIANT



*	390	CARTON:46*30*25CM	A/R	PCS
*	390	PE BAG:30*28*0.08MM	A/R	PCS
*	390	PE BAG:8*10*0.06MM	1	PCS
9	240010800005	SRW-RE32/BLACK10	4	PCS
8	370	FOIL-CU-30MM	65.0*2	MM
7	370	HI TEAMP TAPE:w:26MM	80.0*2	MM
6	120020000001	PE-5321	8.5	G
5	1200100000031	PVC-BLACK10/50	33.0	G
4	2000340000034	TUBE-HT-ø3.0MM(thin)	10.0*8	MM
3	2000340000032	TUBE-HT-ø1.0MM(thin)	15.0*8	MM
2	204-2411101200	D.V.I.-24+KEY-M(BK)	2	PCS
1	1308191100091	28-[<1P+D+A+MYLAR>*7+1P+3C]+FILLER +A+D+B-BK10-8.6U20276	5.0	M
NO	PART NO.	DESCRIPTION	QTY	UNIT

OUTER MOLDING	AV.DVI-053		
INNER MOLDING	AV.DVI-052		
DRAWN, BY: 楊燕瑛		SCALE: NONE	DATE: 2007/12/04
CHECKED, BY:		CUSTOMER: C331(RS)	PAGE: 1/1
APP'ED, BY:		CUSTOMER P/N: 489359	
ITEM: 489359		REV: A	

ALL DIMENSIONS IN mm