

Name: **JONO luminaire**  
1x14W T5/G5 220-240V 0/50-60Hz, 600mm

Type: 796-1820



### Technical specification

Colour: RAL9010

Material: Base aluminium (RAL9010) / diffuser opal polycarbonate

Electronic control gear: x

Enclosure class: IP44

Length (mm): 600 mm

Light source: 1xT5 14W/G5

Operating frequency (Hz): 0/50-60 Hz

Rated power (W): 14W

Rated voltage (V): 220-240 V

Weight (kg): 0.935 kg

Dimensions (mm) lxxhxh: 600x55x87 mm

