





NO	DESCRIPTION	DATE
1	BACKGROUND FORMAT UPDATED	08.12.02
2	MODIFICATION NOTES 4.	10.22.04



MOUNTING HOLE

NOTES: UNLESS OTHERWISE SPECIFIED

- BODIES: BRASS PER JIS-C3604
- CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
- INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- CONNECTOR INTERFACE PER BS EN 122340
- PART TO BE CLEAN AND FREE OF BURRS

APPROVED by _____ DATE: _____ 6560154

5	NUT	BRASS	1	GOLD
4	WASHER	BRASS	1	GOLD
3	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD 30μ" MIN.
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	GOLD 3μ" MIN.
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH



DESCRIPTION		MMCX STRAIGHT BULKHEAD JACK RECEPTACLE							
製圖	DRAWN	TOLERANCE	品名		37-08/ROHS COMPLIANT (50Ω)	日期	DATE	版次	REV.
	Elvis		.X	±0.2					
檢圖	CHECK	.XX	±0.1	單位	DWG.NO.	37-0023			
	Lewis			mm(in)					
認定	APPROV	.XXX	±0.05	比例					
	Lewis			ANGLE	±5°	8:1			