



Accessories

Rep.	Description	Type	Order code	Packaging	Weight kg
For sockets					
1	Lid	CPC-1	1SNA166578R0100	1	
2	Cover (a)	CPC-7	1SNA166734R2500	1	0.07
3	Ring-tongue lug for 10 mm ² wire	CS-10	1SNA167700R1100	10	
4	Socket interlocking peg	CVABM	1SNA183436R0500	10	
5	TH35 rail mounting kit	KEM-3	1SNA166962R0000	10	0.02
6	Mounting kit for DIN 1 rail (a)	FX	1SNA167682R2300	10	
7	Replacement kit for flush mounting (b)	KEM-1	1SNA166928R2000	50	0.02
8	Comb-type jumper bar (b)	PCVA	1SNA167496R1100	10	
9	Comb-type jumper bar IP20 (c)	PCVL	1SNA167681R2200	10	
10	Jumper bar for 2 sockets (c)	BJ-VL	1SNA167680R0500	10	
For plugs					
11	Pin 1 mm ²	BRE-C-1	1SNA167264R0700	10	
	Pin 1.5 mm ²	BRE-C-1.5	1SNA167265R0000	10	
	Pin 2.5 mm ²	BRE-C-2.5	1SNA167260R1700	10	
	Pin 4 mm ²	BRE-C-4	1SNA205876R0400	10	
	Pin 6 mm ²	BRE-C-6	1SNA168146R0200	10	
12	Pin extraction tool	EXBR1	1SNA167008R0300	1	
13	Crimping tool for BRE pins	1 to 2.5 mm ² PSC	1SNA173181R1300	1	
For test					
Ø 4 mm test plugs					
14	IP20 with mobile protection	Red ■ FC4-1	1SNA167927R1000	10	0.01
15	IP20 with permanent protection	Black ■ FC4-5	1SNA167931R1400	10	0.01
16	Bayonet security test plug	Black ■ FCB-1	1SNA167690R0700	10	0.01
		Red ■ FCB-2	1SNA167692R2500	10	0.01
17	Isolating cap for FCB plug	CA	1SNA167697R2200	10	
18	Straight adaptor	IR1	1SNA167622R2600	5	
19	H adaptor (short-circuit bridge)	IR2	1SNA167623R2700	5	
20	Isolating cap for IR1 & IR2 adaptors	DI	1SNA167981R1700	10	0.01
21	Adaptor between FCB plug and ring-tongue test interface	IR3	1SNA167624R2000	10	

(a) Compatible with base mounting only.

(b) Compatible with ring-tongue connection type socket only (VA).

(c) Compatible with screw connection type socket only (VL).

Selection guide

Mounting	Sockets	Lids	Covers	Plugs					
		CPC-1	CPC-7	FIC-2/4-DIA4 Universal plug	FIC-2/1-1	FIC-2/4-2	FIC-2/4-1	FIC-2/4-R rack mounting R	FIC-2/4-I reverse mounting I
TH35 Rail	CC-TH35-VL-6.6	●	●	●	●	●	●		
Base	CC-DS-VL	●	●*	●	●	●	●		
Half-base	CC-E-VA	●		●	●	●	●		
Half-base	CC-D-VA	●		●	●	●	●		
Rack	CC-R-VA			●	●			●	
Reverse	CC-I-VA-2				●				●
Flush with lid	CC-E-VA-6.6			●	●	●	●		

* Nota: CPC-7 compatible with CC-DS-VL socket only in "base" mounting option.