

## 23 W GR

Outdoor LED wall luminaires



---

## Technical data

---

### Electrical data

Nominal wattage	23 W
Nominal voltage	220...240 V
Mains frequency	50/60 Hz
Operating mode	Electronic control gear

### Light technical data

Color temperature	3000 K
Beam angle	110 °
Light color as per EN 12464-1	Warm white
Color rendering index Ra	>80

### Dimensions & weight

Length	210.0 mm
Width	188.0 mm
Height	237.0 mm

### Colors & materials

Body material	PP
Product color	Grey
Cover material	UV-stabilized PC

### Temperatures

Ambient temperature range	-20...+40 °C
---------------------------	--------------

### Additional product data

Equipped with lamp	Yes
--------------------	-----

### Capabilities

Type of installation	Surface-mounted
Type of connection	Terminal, 3-pole
Accessories	Screws / Dovels / Washers

### Certificates & standards

Standards	CE
Protection class	I

## Product datasheet

---

Type of protection	IP44
--------------------	------

---

### Country specific categorizations

---

Order reference	NXL LED HP FLOO
-----------------	-----------------

---

## Product datasheet

---

### Logistical Data

---

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4052899905603	23 W GR	Folding carton box 1	302 mm x 190 mm x 201 mm	11.53 dm <sup>3</sup>	1186.00 g
4052899905665	23 W GR	Shipping carton box 2	330 mm x 219 mm x 399 mm	28.84 dm <sup>3</sup>	3285.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.