

General Information

Extended Product Type:	232MPR4W
Product ID:	2CMA168080R1000
EAN:	7392696680806
Catalog Description:	Switched interlocked socket-outlet with RCD, 4h, 30mA, 32A, IP67, 2P+E
Long Description:	Switched Interlocked Socket Outlet with RCD, earthing sleeve position 4h, 30mA, rated current 32A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Yellow

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets with RCD

Ordering

EAN:	7392696680806
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	130 mm
Product Net Height:	375 mm
Product Net Length:	182 mm
Product Net Depth:	375 mm
Product Net Weight:	1.8 kg

Container Information

Package Level 1 Width:	143 mm
Package Level 1 Length:	397 mm
Package Level 1 Height:	187 mm
Package Level 1 Gross Weight:	1.9 kg
Package Level 1 EAN:	7392696680806
Package Level 1 Units:	1 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---------------------------------------------------------------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, knock-outs 2xØ25mm
Cable Cross-Section:	2.5 ... 10 mm ²
Cable Entry Position:	Top
Cable Outlets Per Side:	2xØ25
Color:	Yellow
Degree of Protection:	IP67
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz
Function:	Switched interlocked socket outlet with RCD, 30 mA
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#232MPR4W
Number of Poles:	3
Number of RCD 30mA:	1
Number of RCDs:	1
Object Classification Code:	2CMT005069
Product Main Type:	MPR
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Watertight
Rated Current (I _n):	32 A
Rated Residual Current:	30mA

Rated Voltage (U_r):	100 ... 130 V
RoHS Date:	L23
Standards:	IEC 60 309-1, -2, -4
Suitable For:	Switched Interlocked Socket Outlets with RCD
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-number:	2466215
UNSPSC:	39120000

