

Datasheet

RS Pro Right Angle 75Ω PCB Mount BNC Connector, jack, Crimp Termination Nickel

RS Stock No: **546-5171**



Product Details

RS Pro PCB mount BNC connector has a nickel plated body and gold plated centre contact. This 75 Ω right angle BNC connector comes with cable crimp termination.

Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Jack, crimp termination

Specifications:

Body Orientation	Right Angle
Body Plating	Nickel
Contact Material	Phosphor Bronze
Contact Plating	Gold
Gender	Female
Impedance	75 Ω
Mounting Type	PCB Mount
Operating Frequency	0 to 1 GHz
Polarity	Normal
Termination Method	Crimp
Body Material	Zinc Alloy
Insulation Material	PP
Insulation Resistance	5000 MΩ
Operating Temperature Range	-40 to +60°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)