



CATALOG LISTING

ABN1150

 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE — — — 3.5 OZ MAX		CONTACT ARRANGEMENT S P D T		DO NOT SCALE PRINT	
RELEASE FORCE — — — — 1 OZ MIN		-L33- 20 A-125, 250, OR 480 VAC 1 HP-125 VAC; 2 HP-250 VAC 0.3 A-125 VDC; 0.15 A-250 VDC	   	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±	
PRETRAVEL — — — — .290 MAX					
A DIFFERENTIAL TRAVEL — — .024 MAX					
OVERTRAVEL — — — — .062 MIN					
		-L288-	20(3)A 250V ~ T85 5E4		
		-L308-			
		-L315-		WEIGHT	