

316MHS6W



Products Low Voltage Products and Systems Industrial Plugs and Sockets Plugs & Sockets
Switched Interlocked Socket Outlets, Horizontal

General Information

Extended Product Type:	316MHS6W
Product ID:	2CMA167809R1000
EAN:	7392696678094
Catalog Description:	Switched interlocked socket-outlet, 6h, 16A, IP67, 3P+E
Long Description:	Switched Interlocked Socket Outlet, horizontal, earthing sleeve position 6h, rated current 16A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

Additional Information

Additional Information:	Cable entry, knock-outs Ø25mm/M25
Cable Cross-Section:	1.5 ... 4 mm ²
Cable Entry Position:	Top and bottom
Cable Outlets Per Side:	1xØ25
Color:	Red
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	acc. to IEC 60529 IP67
E-nummer:	2416902
EAN:	7392696678094
ETIM 4:	EC001324 - CEE socket outlet, disconnectable, with fuse
ETIM 5:	EC000140 - CEE plug
ETIM 6:	EC000140 - CEE plug
Enclosure Material:	Thermoplastic
Environmental Information:	2CMC700001D0002
Frequency (f):	60 Hz
Function:	Switched interlocked socket outlet, horizontal
Gross Weight:	0.58 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#316MHS6W
Minimum Order Quantity:	1 piece
Mounting Type:	Horizontal
Number of Poles:	4
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696678094
Package Level 1 Gross Weight:	0.58 kg
Package Level 1 Height:	200 mm
Package Level 1 Length:	140 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	135 mm
Product Main Type:	CMHS

Product Name:	Industrial Switched Interlocked Socket Outlet
Product Net Depth:	129 mm
Product Net Height:	129 mm
Product Net Length:	126 mm
Product Net Weight:	0.58 kg
Product Net Width:	168 mm
Protection Type:	Watertight
Rated Current (I_n):	16 A
Rated Voltage (U_r):	380 ... 415 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
Selling Unit of Measure:	piece
Short Description:	Switched interlocked socket-outlet, 6h, 16A, IP67, 3P+E
Size:	126X168X129
Standards:	IEC 60309-1 IEC 60309-2 IEC 60309-4
Suitable For:	Switched Interlocked Socket Outlets, Horizontal
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour

