

SOCKET OUTLET 6P+E IP67 32A 6h






TechData

Rated current	32A
Commercial series	OPTIMA-SEVEN Series
Poles	6P+E
Hour position	6h
Rated voltage	380-415V
Working frequency	50Hz
Working frequency	60Hz
Colour	RED
Syntetical description	SOCKET OUTLET
Protection degree	IP66/IP67
Types of available outlets	ANGLED

Approvals and Certifications

CE CE Declaration of conformity

Standards and Laws

-  EN 60309-1 (1999) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A1 (2007) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A2 (2012) [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

Packaging

Description	
Quantity	
Gross weight	
Volume	
Dimensions	

	Box
	5
	2.15 KG
	11599.5 CCM
	185x285x220 (MM)