


Stromlaufplan/schematic diagram




Abschirmung auf M12 Rändelschraube 360°aufgelegt
shielding disposed 360° on M12 knurled screw



PUR-Leitung 2x2xAWG22/7 in grün
PUR-conductor 2x2xAWG22/7 in green

21 03 485 1440	40,0m
21 03 485 1425	25,0m
21 03 485 1415	15,0m
21 03 485 1410	10,0m
21 03 485 1405	5,0m
21 03 485 1403	3,0m
21 03 485 1401	1,0m
Artikelnr.	Nennlänge (L)



ALL Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
413513	11.12.07	Ho		Dat.	Name	1:1	M12-Rundsteckverbinder M12-circular connector Stift, gerade, 4polig, AWG 22, D-kodiert, umspritzt male, straight, 4poles, AWG 22, D-coded, cable extrusion
412507	26.10.06	DY	Detail.	06.01.05	Ho		
412334	20.07.06	Grie	Insp.		WELL		
412196	05.05.06	DY	Stand.				
411650	08.06.05	DY	HARTING Electric GmbH & Co. KG				TB 21 03 485 1400
411621	17.05.05	DY	D-32339 Espelkamp				
Mod.	Dat.	Name					Blatt/ page