



LED Lenser's i² is the smallest hand torch in its i-Series range but still features bullet-proof build quality, Advanced Focus System optics and a 170-metre beam range. Measuring just 101mm in length and weighing only 110g it's a handy torch for any craftsman, inspectors or construction workers that will not take up too much room in an overall pocket or workbench. Fitted with a CREE® Power LED Light Chip for bright white light it has gold-plated contacts inside a rugged metal body, along with one-handed Speed Focus for easy handling. Those out on site will welcome its simple operation from just three AAA batteries (supplied).

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Robust handheld torch
- CREE® Power LED Light Chip
- Battery cartridge (for 3 x AAA batteries)
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Speed Focus®
- Water-resistant (IPX4)
- Gold-plated contacts

Technical Information

Power: 105 lumens max

Run Time: up to 6.5 hours

Beam Distance: up to 170m

Weight: 110grams

Supplied with : Safety bag, Pouch, Lanyard, Batteries (3xAAA)

Code	Description	Unit Colour	Packaging	Barcode
5602	i ²	Black	Box	4029113560207

RRP ex.vat £24.96 / incl.vat £29.95