




ENGLISH


Datasheet

RS Pro Crimp Tool Open Barrel Terminal, 0.1 → 1.5 mm² Wire Size

RS Stock No.683-1620



Die profile



Crimp profile

DRB-0115 is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on uninsulated open barrel connectors on wires ranging from 0,10-1,5 mm².

Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information See instruction sheet.

- Compact, pocketable design.
- Ergonomic handles for low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable - minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to guarantee performance.

Technical data

Length :	198 mm/7,80"
Height :	65 mm/2,56"
Weight :	350 gr/0,77 lbs
Connector:	Open barrel
Description:	Uninsulated
Wire size awg:	26-16 AWG
Wire size mm ² :	0,10-1,5 mm ² / 26-16 AWG