



MAGNESIUM ENCLOSURE

Solid material, ultra lightweight, keeps your hard drive cool and is environment-friendly.



POWER VIA USB PORT
NO POWER ADAPTER NEEDED



NO FAN - NO NOISE
SILENT OPERATION



ULTRA THIN DESIGN
WORLD'S THINNEST MOBILE DRIVE



MOBILE DRIVE Mg

EXTERNAL PORTABLE STORAGE FOR MAC / USB 3.0 / USB 3.0 & FIREWIRE 800

External portable storage - designed for Mac

- Ultra thin mobile hard drive in stylish design, complements the design of your MacBook
- Magnesium enclosure: ultra lightweight, high quality, solid and environment-friendly material
- Connects to the USB port of your MacBook / U&F version also connects to the FireWire800 port of your MacBook
- Mac HFS+ formatted, immediately ready to be used on your MacBook and 100% Time Machine® compatible
- Power via USB port, no need to carry a bulky power adapter
- Excellent value for money
- No cooling fan, ensures quiet operation
- High quality and sleek design, only 12 x 8.1 x 1 cm or 12 x 8.1 x 1.5 cm
- Two years manufacturer's warranty and unlimited free helpdesk support

Available in multiple versions:

- USB 3.0 slimline - 320GB - only 1cm thin, using the latest state of the art 7mm slimline internal hard drives
- USB 3.0 - 750GB - 1.5cm thin, which is still thinner than most mobile hard drives
- USB 3.0 & FireWire800 - 750GB - 1.5cm thin, with FireWire800 interface for optimal flexibility, ideally suited for audio and video editing purposes

Why magnesium?

- **Solid** - Magnesium has the best strength-to-weight ratio of any of the commonly used structural metals, has excellent dimensional stability and is highly impact and dent resistant
- **Lightweight** - Magnesium is the lightest of all the commonly used metals (50 to 60% lighter than aluminium)
- **Cool** - Magnesium has the same characteristics as aluminium - it keeps an enclosure cool, dissipates the heat - no noisy cooling fan required!
- **Green** - Magnesium is an earthly matter. It is produced from sea water, brines and magnesium-bearing minerals, which offer unlimited reserves.

The perfect mobile hard drive next to your MacBook!

The Freecom Mobile Drive Mg has been specifically designed as storage expansion for your MacBook. Available in capacities up to 750GB and in USB 3.0 and USB 3.0&FireWire800 versions, there will always be a Mobile Drive Mg which exactly suits your needs.

Ready for the future

The Mobile Drive Mg is equipped with a USB 3.0 interface. USB 3.0 is the successor of USB 2.0 and provides a theoretical transfer speed increase of 10x compared to USB 2.0! Don't have a computer with USB 3.0 ports yet? Don't worry - the Mobile Drive Mg is fully downwards compatible with USB 2.0 so you can use it without any problem on any computer with a USB 2.0 port.

Made from Magnesium

The enclosure of the Mobile Drive Mg is made from magnesium. Magnesium is a solid, lightweight, cool and environment-friendly material. Combined with the elegant and sleek design, the use of Magnesium has resulted in a perfect match for your MacBook

100% Mac!

The Freecom Mobile Drive Mg is Mac HFS+ formatted and can be optimally used with your Mac from the moment you connect it to the USB port of your Mac or MacBook. It is 100% TimeMachine compatible, ideal for making backups of your important data!

The Freecom Mobile Drive Mg is exclusively available at Apple resellers



MOBILE DRIVE Mg

PRODUCT SPECIFICATIONS FREECOM MOBILE DRIVE Mg:

CAPACITY: 320GB (Slim), 750GB, 750GB (U&F)

INTERFACE: USB 3.0, USB 3.0 & FireWire800 (U&F model only). Can also be connected to USB 2.0*

HARD DRIVE TYPE: 2.5" SATA, low noise, low power consumption. The slimline model uses a 7mm formfactor 2.5" SATA hard drive inside.

DATA TRANSFER SPEED: Max. 5000Mbit/s (USB 3.0) / max. 800Mbit/s (FireWire 800), theoretical maximum data transfer speeds

POWER REQUIREMENTS: powered by computer through USB port, no power adapter required

MTBF: 50.000 P.O.H.

WEIGHT: 170 g (slimline version) / 200 g

DIMENSIONS: 12 x 8.1 x 1 cm (slimline version) / 12 x 8.1 x 1.5 cm / 12.8 x 8.1 x 1.5 cm (U&F)

ENVIRONMENTAL SPECIFICATIONS:

Operating temperature: 10° C / 35° C

Storage temperature: -20° C / 70° C

MINIMUM SYSTEM REQUIREMENTS:

MAC: PowerPC G4/G5 or Intel Mac, 512MB RAM or higher, available USB port, Mac OS X v10.4 or higher

This drive is Mac HFS+ formatted. For use on Windows computers the drive needs to be reformatted (formatting software tool included).

* When connected to USB 2.0 port, the data transfer speed will be according to USB 2.0 specification.

PACKAGE INCLUDES:

- Freecom Mobile Drive Mg
- USB connection cable
- FireWire800 connection cable (U&F model only)
- Quick Install Guide
- Free unlimited helpdesk support
- Two years manufacturer's warranty

Mobile Drive Mg	320GB (slimline) USB 3.0	750GB USB 3.0	750GB U&F (USB 3.0 & FireWire800)
Art.-Nr. EU/UK	35734	35742	35737
EAN-Code EU/UK	4021801357342	4021801357427	4021801357373
Colour	Silver	Silver	Silver