

## ToLEDo Retro A60

ToLEDo RT A60 806LM B22 SL

0027126

### Range features



### PRODUCT OVERVIEW

Ordering number	0027126
Technology	LED
Light colour	Homelight
Energy class	A++
Average life (Rated) (h)	15000
Lamp shape	A60
Lamp finish	Clear
Dimmable	No
Cap/Base	B22
Type	ToLEDo Retro A60
EAN code	5410288271262
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	806
Efficacy (Rated) (lm/w)	134.33
Watt (Nominal) (W)	6
Equivalent watt (W)	60
Voltage (V)	230-240

# ToLEDo Retro A60

ToLEDo RT A60 806LM B22 SL

**0027126**

## DATA TABLE

### General data

Dry applications use only	Yes
Technology	LED
Ordering number	0027126
Energy saving lamp	Yes
Energy class	A++
Average life (Rated) (h)	15000
Average life (Nominal) (h)	15000
Lamp finish	Clear
Lamp shape	A60
Dimmable	No
Cap/Base	B22
Type	ToLEDo Retro A60
EAN code	5410288271262
Product name	ToLEDo RT A60 806LM B22 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
General application	Hospitality; Residential & Consumer
Intended purpose	No
No. of switching cycles before premature failure (min)	20000
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

### Optical data

Light colour	Homelight
CRI (Ra)	80
Suitable for accent lighting	No
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	806
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	806
Adjustable chromaticity	No

## ToLEDo Retro A60

ToLEDo RT A60 806LM B22 SL

0027126

### Electrical data

kWh per 1000 hours burning time	6
Efficacy (Rated) (lm/w)	134.33
Watt (Nominal) (W)	6
Watt (Rated) (W)	6
Equivalent watt (W)	60
Voltage (V)	230-240
Drive current (mA)	52
Lamp power factor	0.5

### Physical data

Lamp Length (mm) - C/L	103
Max. Lamp Diameter (mm) - D	60
Lamp dimension equal to filament lamp equivalent	Yes

## ENERGY LABEL

