



ENGLISH

Datasheet

Red 30m Nylon Air Hose, -40 → +80°C, Application Various

RS Stock number 4835579



Features

Standard Nylon Tube

Suitable for most pneumatic requirements in or out of the control cabinet. Available in 6 colours

Suitable for use with pneumatic fittings

Manufactured to BS 5409 (part 1) 1976- IS07628/1

Maximum working pressure =>21 bar

Burst pressure =>63 bar

Operating temperature range -40 to 80°C

30m coils

Push-in System - Nylon Tube

All coils shown are non anti-static.