




900M-T-B Shape-B




900M-T-2C Shape-2C




900M-T-3C Shape-3C




900M-T-4C Shape-4C




900M-T-K Shape-K




900M-T-1.6D Shape-1.6D




900M-T-2.4D Shape-2.4D




900M-T-3.2D Shape-3.2D



900M-T-2CF Shape-2C
Tinned cut surface only



900M-T-3CF Shape-3C
Tinned cut surface only



900M-T-4CF Shape-4C
Tinned cut surface only