





NO	DESCRIPTION	DATE
①	ACCESSORIES REMOVED	12.06.03
②	BOBBIN → PRESS PIN	09.12.06'
③	TIN → TIN 40μ"MIN.	02.20.08'



09/02/2013



MOUNTING HOLE

(P/N:5462706)

APPROVED

by

DATE:

1.0 ELECTRICAL

1.1 FREQUENCY RANGE: DC-1 GHz

1.2 NOMINAL IMPEDANCE: 75 OHM

2.0 MATERIALS

2.1 BODIES: BRASS PER JIS-C3604

2.2 CENTER CONTACT: BRASS PER JIS-C2680

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

4.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
4	NUT	BRASS	1	NICKEL
3	WASHER	BRASS	1	NICKEL
2	PRESS PIN	PP+BRASS	1	TIN 40μ" MIN.
1	BODY	BRASS	1	NICKEL 100μ" MIN.



DESCRIPTION		F STRAIGHT BULKHEAD JACK RECEPTACLE	
製圖	DRAWN	TOLERANCE	品名
檢圖	CHECK	單位	UNIT
認定	APPROVAL	比例	SCALE
	Yoko	.X ±0.2	18-19 PP.T.N
	Ivan	.XX ±0.1	\ROHS COMPLIANT (<75Ω)
	Angela	.XXX ±0.05	DATE 03.04.93'
		ANGLE ±5°	版次 A-3
			DWG.NO. 18-0113