



G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K2	REVISED PER ECO-13-008373	20MAY2013	KH	DR



AMP
WIRE RANGE

12-10 AWG
SOLID OR STRANDED

- 1
- STAMP AMP 12-10, APPROX AS SHOWN
-
- 2
- WIRE BARREL COLOR CODED ORANGE TO DENOTE NICKEL MATERIAL
-
- 3
- NICKEL PER ASTM B-162, ANNEALED
-
- 4
- NOTE DELETED.



50	LOOSE PIECE , BOX	8-323745-2
2500	323745 ON TAPE	2-323745-6
--	LOOSE PIECE	323745
QTY	PACKAGE TYPE	PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE:
649°C[1200° F]

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
2.62-6.64mm²[5,180-13,100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
- 3

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN JR RUTH 20MAR09
CHK T MICHELUTTI 20MAR09
APVD T MICHELUTTI 20MAR09
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -
CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL, RING TONGUE,
HIGH TEMPERATURE,
STRATO-THERM

SIZE A2
CAGE CODE 00779
DRAWING NO C-323745
RESTRICTED TO -

SCALE 10:1
SHEET 1 OF 1
REV K2

1471-9 (3/11)