



ENGLISH

Datasheet

DC Axial Fan, 40 x 40 x 20mm, 15.3m/h, 2.16W, 24 V dc (OD4020 Series)

RS Stock number [619-7065](#)




RS Part Number	Orion Part Number	Speed (RPM)	Airflow (CFM)	Noise (db)	Volts (DC)	Voltage Range	Current (Amps)	Lead Type
6197059	OD4020-12HB(01A)	7800	9	32	12	7~14	0.15	Wire
6197065	OD4020-24HB(01A)	7800	9	32	24	10~27	0.09	Wire

Frame and Impeller
PBT, UL94V-0 Thermoplastic

Available Options
Tachometer
Locked Rotor Alarm

Finger Guard: G40-2
Plastic Guard: G40P
Filter Kit: GRM40-30, GRM40-45

Drawing(mm):



*Drawing for Dimensional Reference Only

MOTOR

Brushless DC, polarity protected, locked rotor protected (current limited), auto restart

INSULATION RESISTANCE

Min. 10 M ohms at 500VDC

LIFE EXPECTANCY (L10)

Ball Bearing 60,000 Hours

Operating Temperature

-10C ~ +70C

Safety Approvals

UL/CUL, TUV, CE