

Protective covers - VC-SD-T2 - 1886731

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

VARIOCON protective cover for sleeve housing, with IP50 protection, type 2, max. tightening torque: 1.6 Nm



The illustration shows the version VC-SD-T1

Why buy this product

- Easy mounting
- Contact inserts are protected when not plugged in



Key commercial data

Packing unit	5 pc
GTIN	 4 017918 908423
Weight per Piece (excluding packing)	18.52 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 80 °C

General

Type	VC2
	For sleeve housing
Material	PA
Inflammability class according to UL 94	V0
Color	gray
Seal present	No
Assembly instructions	Tightening torque: 1.6 Nm

Protective covers - VC-SD-T2 - 1886731

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27142104
eCl@ss 5.1	27142104
eCl@ss 6.0	27142104
eCl@ss 7.0	27142104
eCl@ss 8.0	27142104

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002040
ETIM 5.0	EC002040

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Drawings

Dimensioned drawing

