

Datasheet

DIN Connector Sockets, ME - 209/SL-*

RS Stock number 811-8279



Specifications:

Connection Type:	2 Pole + Earth
Voltage:	12 VDC / 24 VDC / 48 VDC / 110 VDC / 250 VDC / 110 VAC / 250 VAC
Approvals:	N.A.
Standard:	N.A.
Mounting:	Screw-type
Type:	ME-Socket - Illuminated
Socket Type:	Type A
DC V Range:	12,24, 48
Mounting:	M3 Screw
Material For Rubber Gasket:	Nitril / Silicon
Material Body:	Polycarbonate
Gland Size:	PG-9
Body Colours:	Transparent Body
Contact Resistance (Initial):	20 m Ohms max. (Initial)
Current Carrying Parts:	Copper Alloy, Tin plated
Permissible Temp. With/Without Load:	0°C to 90°C
Rating:	10A 110VAC, 230VAC
Terminals:	Screw-type
H. V. Breakdown Test:	2KV AC For 1 Minute .
Insulation Resistance:	100 M Ohms min.

Unit mm

