

Datasheet

RS Pro DC Axial Fan, 60 x 60 x 10.45mm, 36m³/h, 3W, 12 V dc (OD6010 Series)

RS Stock No: **789-7860**



Product Details

RS Pro DC axial fan measures 60 x 60 x 10.45 mm. It has a power rating of 3 W and voltage rating of 12 V dc. This sealed-sleeve axial fan delivers a superior airflow of 36m³/h with a rotating speed of 4600 rpm. It is suitable for general purpose applications. The sealed sleeve technology retains bearing lubricant, increasing fan life.

Features and Benefits

- Comes in black colour
- Sealed sleeve technology retains bearing lubricant
- Long life expectancy of more than 50,000 hours

**Specifications:**

AC or DC Operation	DC
Air Flow	36 m ³ /h
Bearing Type	Sleeve
Configuration	Square
Depth	10.45 mm
Dimensions	60 x 60 x 10.45 mm
Direction of Curve	Radial
Fan Speed	4600 rpm
Height	60 mm
Noise Level	36 dB
Power Consumption	3 W
Special Features	Brushless DC, Auto Restart, Impedance & Polarity Protected Motor
Static Pressure	0.16 inH ₂ O
Supply Voltage	12 V dc
Termination Type	Lead Wire
Width	60 mm
Frame Material	PBT
Impeller Material	Plastic
Insulation Resistance	10 MΩ
Life Expectancy	60000 h
Standards Met	UL, cUL, TUV