





TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



PORTABLE TOOLS TRANSFORMER

TYPE: ISOLATION

INPUT: 230V 50Hz

OUTPUT: 230V

RATING: 3KVA INTERMITTENT
5MINS ON 15MINS OFF

THERMAL CUT-OUT: 10A

OUTPUT SOCKET: 2x13A BS1363
RATED IP44

INPUT PLUG: 13A BS1363

ENCLOSURE: GRP
RATED IP55

COLOUR: BLUE

REV	4		CARROLL & MEYNELL TRANSFORMERS LIMITED TEL: 01642 617406 FAX: 01642 614178 enquiries@carroll-meynell.com	TITLE	DRAWN	PROJECTION	DATE	SCALE	
	3			PORTABLE TOOL	SH		26/4/8	NTS	
	2			TRANSFORMER CM3000/230	DRAW No			REV	PAGE
	1			ALL DIMENSIONS IN mm	3262		0	1/1	