

## RS 9/15/30kW Fan Heaters

RS Stock No.: 839-5283

RS Stock No.: 839-5286

RS Stock No.: 839-5280



	839-5283	839-5286	839-5280
Max. Airflow rate	980 m <sup>3</sup> /hour	1100 m <sup>3</sup> /hour	1900 m <sup>3</sup> /hour
Heating Capacity	4.5 / 9 kW	5 / 10 / 15 kW	15 / 30 kW
Current Consumption	13 A	21.7 A	43.3 A
Input Voltage	400 V / 50 Hz	400 V / 50 Hz	400 V / 50 Hz
Sound Level	55 dB	57 dB	61 dB
Dimensions	340 / 335 / 410 mm	395 / 380 / 445 mm	860 / 565 / 645 mm
Weight	10.8 kg	19 kg	32.5 kg