

Datasheet

RS Pro IP44 Purple Panel Mount 2P Industrial Power Socket, Rated At 16A, 20 to 25 V

RS Stock No: **668-5367**



Product Details

RS Pro IP44 purple panel mount 2P industrial power socket has a voltage rating of 20 to 25 V, current rating of 16 A and temperature rating of -25 to +40°C. It features robust design with plastic construction for durability. This splash proof, female socket is well suited to industrial purposes.

Features and Benefits

- Low voltage panel socket
- This splash proof, female socket is well suited to industrial purposes
- Made from engineering plastic
- Screw down termination method

**Specifications:**

Body Orientation	Straight
Colour	Violet
Current Rating	16 A
Gender	Female
IP Rating	IP44
Low Voltage	Yes
Maximum Operating Temperature	+40°C
Minimum Operating Temperature	-25°C
Mounting Type	Flush Mount
Plug/Socket	Socket
Pole Format	2P
Termination Method	Screw Down
Voltage Rating	20 to 25 V
Operating Frequency	50/60 Hz
Standards Met	IMQ - ENEC 03, EN 60309-1, 2