



ENGLISH

Datasheet

Stock No: 429-688

RS Pro PE Flexible Conduit Grey 10mm IP55 5m



Product Details

IP55 conduit

A low cost flame retardant, general purpose conduit resilient to prolonged flexing and vibration. Manufactured from extrusion drawn polyethylene.

IP55 conduit (when used with compatible fittings, available separately)

Conduit -50 → 100°C, fittings -25 → 50°C operating temperature

Crush resistant to BS6099

Resistant to: nitric acid, sulphuric acid, detergent, diesel and white spirit

Specifications:

Nominal Diameter	10mm
Conduit Type	Flexible
Material	PE
Colour	Grey
Interior Diameter	7.4mm
Outer Diameter	10.2mm
Length	5m
IP Rating	IP55
Minimum Operating Temperature	-50°C
Maximum Operating Temperature	+100°C
Minimum Bend Radius	9 mm

