

## MB5A10F4

Article Number: 151-00427

Adhesive Bases, .35" Max tie width, .19" Hole Dia., 1.49" Length/Width, PA66, White, 250/pkg



Download spec sheet

### Base Data

**Local Order Number** MB5A10F4

**Type** MB5A

**Color** White (WH)

- Features and Benefits**
- For use with 18 and 30 pound cable ties to provide stability when securing bundles.
  - Secures with rubber based adhesive backing and/or two or four screws.
  - 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.

**Product Description** HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.

**Fixation Method (FF)** Screw Mounting and Adhesive

**Short Description** Adhesive Bases, .35" Max tie width, .19" Hole Dia., 1.49" Length/Width, PA66, White, 250/pkg

### Product Dimensions

**Length L (imperial)** 1.49 "

**Length L (metric)** 37.7 mm

**Width W (imperial)** 1.49 "

**Width W (metric)** 37.7 mm

**Cable Tie Width Max (imperial)** 0.35 "

**Cable Tie Width max. (metric)** 8.9 mm

**Height H (imperial)** 0.28 "

**Height H (metric)** 7.1 mm

**Mounting Hole Diameter D (imperial)** 0.19 "

**Mounting Hole Diameter D (metric)** 4.8 mm

**Mounting Hole Centers (imperial)** 1.0 "

**Mounting Hole Centers (metric)** 25.3 mm

### Logistics and Packaging

**Quantity per** bag

**Package Quantity** 250

**Carton Quantity** 2000

### Material and Specifications

**Material** Polyamide 6.6 (PA66)

**Material Shortcut** PA66

**CSA Certified** No

**Flammability** UL94 V2 (excluding adhesive)

**Operating Temperature** -40°F to +185°F (-40°C to +85°C)

**ROHS Conformity** Yes

**UL Listed (US and Canada)** No

**UL Recognized (US and Canada)** Yes