

# Interface module - UM 45-D50SUB/S - 2962816

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




VARIOFACE module, with screw connection and D-subminiature pin strip, for assembly on NS 35/7.5, 50 positions (no consecutive numbering)

The illustration shows the version UM 45-D37SUB/S



## Key commercial data

Packing unit	1 pc
GTIN	 4 017918 087470
Weight per Piece (excluding packing)	136.85 g
Custom tariff number	85369010
Country of origin	Germany

## Technical data

### Dimensions

Width	156 mm
Height	45 mm
Depth	42 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

### General

Nominal voltage $U_N$	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
	1.5 A (with even load on all branches)
Number of positions	50
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	any

# Interface module - UM 45-D50SUB/S - 2962816

## Technical data

### General

Standards/regulations	IEC 60664
	DIN VDE 110
Pollution degree	2
Surge voltage category	II
Rated surge voltage	1.2 kV
Rated insulation voltage	125 V

### Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	1.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	1.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	16
Stripping length	6 mm
Screw thread	M3

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421

# Interface module - UM 45-D50SUB/S - 2962816

## Classifications

### UNSPSC

UNSPSC 13.2	39121421
-------------	----------

## Approvals

### Approvals

#### Approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized

#### Ex Approvals

#### Approvals submitted

## Approval details

UL Recognized	
mm <sup>2</sup> /AWG/kcmil	30-14
Nominal current I <sub>N</sub>	2.5 A
Nominal voltage U <sub>N</sub>	125 V

cUL Recognized	
mm <sup>2</sup> /AWG/kcmil	30-14
Nominal current I <sub>N</sub>	2.5 A
Nominal voltage U <sub>N</sub>	125 V

GOST	
------	--

cULus Recognized	
------------------	--

## Interface module - UM 45-D50SUB/S - 2962816

### Accessories

#### Accessories

#### System cable

Cable - CABLE-D50SUB/B/S/ 50/KONFEK/S - 2302269



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 0.5 m

---

Cable - CABLE-D50SUB/B/S/100/KONFEK/S - 2302272



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 1 m

---

Cable - CABLE-D50SUB/B/S/150/KONFEK/S - 2302285



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 1.5 m

---

Cable - CABLE-D50SUB/B/S/200/KONFEK/S - 2302298



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 2 m

---

Cable - CABLE-D50SUB/B/S/300/KONFEK/S - 2302308



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 3 m

---

## Interface module - UM 45-D50SUB/S - 2962816

### Accessories

Cable - CABLE-D50SUB/B/S/400/KONFEK/S - 2302311



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 4 m

---

Cable - CABLE-D50SUB/B/S/600/KONFEK/S - 2302324



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 6 m

---

Cable - CABLE D-SUB-S/.../.../... - 2302340



Shielded round cable, assembled with one D-SUB male and one female connector, variable cable length

---

Cable - CABLE D-SUB-B-B-S/.../.../... - 2302421



Shielded round cable, assembled with two D-SUB female connectors, variable cable length

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/0,5M - 2926292



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 0.5 m.

---

## Interface module - UM 45-D50SUB/S - 2962816

### Accessories

Cable - CABLE-D-50SUB/F/OE/0,25/S/1,0M - 2926302



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 1 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/1,5M - 2926315



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 1.5 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/2,0M - 2926328



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 2 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/3,0M - 2926331



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 3 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/4,0M - 2926344



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 4 m.

## Interface module - UM 45-D50SUB/S - 2962816

### Accessories

Cable - CABLE-D-50SUB/F/OE/0,25/S/6,0M - 2926357



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 6 m.

Cable - CABLE-D-50SUB-F-OE-0,25-S/... - 2900908



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: variable.

### Drawings

Circuit diagram

