

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
Article No.	114866
Brady Material No.	B-499
Material Type	Nylon Cloth
Colour	White
Finish	Matt
Order Reference	M71-98-499
Printer Compatibility	BMP71
Size - Diameter	9.53
Size - Height (mm)	9.53
Size - Width (mm)	25.40
Additional Information	Low profile;High adhesion
Thickness (mm)	0.166
Total Qty per Pack	500 Label(s) / Box
Vertical Repeat (mm)	12.70
Approval/Compliance	UL Recognised;CSA Accepted;Halogen Free (DIN VDE 0472/part 815)
Ribbon Series	M71-R4300
Application	Laboratory Identification
Environment	Freezer; Liquid Nitrogen; Autoclave
Industry	Laboratory;Healthcare
Laboratory Application	Centrifuge, Eppendorf & PCR Tubes;Vials & Tubes;Vial Tops;Cryo Tubes
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Service Temp. °C	90
Min. Service Temp. °C	-40

