



fitted with

work equipment
connected load
power consumption
glare-free
system of protection
class of protection
technology
usage
luminaire body
material
color
lamp cover
weight (net)
mains lead

4 x 6W LED
color temperature 5000K
color rendering index (CRI) = 65
without
24V DC
approx. 24W
without
IP67
III
switchable
without switch

anodized aluminum
silver
4mm thick borosilicate safety glass
approx. 2lb (0.9kg)
built-in plug

fastening
total length
special features

fixed surface mount
27.83in (707mm)
30° beam angle

illuminance

measuring conditions: d=50cm

E_{min}: 72 lx
E_m: 1107 lx
E_{max}: 3477 lx

