

LED LENSER® H5 HEAD LAMP

An excellent everyday head torch for safety-conscious hands-free lighting. On the back of the headband it has a battery pack with a red light that makes the wearer easier to see from behind. It's probably this extra safety feature that has made the H5 especially popular with runners, cyclists and night walkers. Anyone though will appreciate the outstanding light performance generated from the energy efficient CREE LED, which can be angled across 90 degrees, has a focusable beam effective up to 70 metres and incorporates the world-leading Advanced Focus System - patented optical technology providing smoother, more consistent transition from spot to flood light. All components are splash-proof for wet weather protection. For wearer comfort there is an adjustable head band made from soft elasticated fabric plus a storage pouch with belt loop to keep it pristine when not in use. Powered by 3 x AAA batteries (supplied).

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Elegant and technologically advanced Head Lamp
- Energy efficient CREE Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Swivelling lamp head for directional 90° lighting
- Glowing red safety back-light
- Lightweight, comfortable and adjustable head strap
- Stretch safe flexi-cable
- Water and dust resistant. IPX54

Technical Information

Power: 25 lumens max

Run Time: up to 20 hours

Beam Distance: up to 75m

Weight: 120grams

Supplied with : Belt Pouch and Duracell® batteries (3xAAA)

Code	Colour	Packaging	Barcode
7495TP	Black	Test-It	402911378690