

Leveling Castor – RS 6114442



ISO view



Side view

Bracket

- ▶ Pressed steel plate with khaki powder coating
- ▶ Aluminum die-casting bracket with bi-level balls upon ball seats in the swivel head
- ▶ Carbon steel handle, wide back access to level
- ▶ Aluminum cushion to stand, anti-vibration function
- ▶ Ivory texture powder coating and zinc-galvanized

Wheels

- ▶ High quality nylon
- ▶ High abrasion resistance, shock and impact-resistant, corrosion-resistant, high chemical resistance to alcohol, salts and certain acids, black color
- ▶ No bearing

Technical Data

Wheel Diameter	75 mm
Width of Tread	30 mm
Hardness of Tread	70 Shore D
Size of Plate	95 x 95 mm
Plate Hole Centers	70 x 70 mm
Plate Hole	11 mm
Leveling Extent	12 mm
Offset	52 mm
Overall Height	120 mm
Temperature	-10 ~ +90°C
Load Capacity / 1pcs	1,000 kg
Load Capacity / 4pcs	2,000 kg

