

EM-DUO 120/20/GFI/AUX/NO

Order No.: 5602192

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=5602192>

Rail-mountable double socket without profile with fault current protective equipment, for mounting on 35 mm DIN rails in acc. with EN 60715, housing color: White, with screw connection, national version: USA

Commercial data

EAN	4046356126236
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	0.3214 KG

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	120 V AC
Nominal current I_N	20 A
For country-specific use in	USA
Color	white
Ambient temperature (operation)	-40 °C ... 70 °C
Width	82 mm
Height	62 mm
Depth	135 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24

Conductor cross section AWG/kcmil max	10
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M3

Certificates / Approvals



Certification

CUL Listed, UL Listed

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2009 Phoenix Contact
Technical modifications reserved;