


LOC	DIST	REVISIONS				
AA	20	P	LTR	DESCRIPTION	DATE	DWN
			U	REVISED; EC 0UF0-0169-01	15OCT01	DLD
						APVD
						EWB

- 1

MATERIAL: POLYPHENYLENE OXIDE MOLDING COMPOUND. SEE TABLE FOR COLOR.
2.

ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3.

100 KITS BULK PACKAGED.



12.19-13.97 [.480-.550]	ALMOND	4-552007-2	4-552006-2	4-552008-2
12.19-13.97 [.480-.550]	BLACK	4-552007-1	4-552006-1	4-552008-1
8.38-9.65 [.330-.380]	BLACK	3-552007-1	3-552006-1	3-552008-1
9.65-10.92 [.380-.430]	BLACK	2-552007-1	2-552006-1	2-552008-1
10.92-12.45 [.430-.490]	GRAY	552007-4	552006-4	552008-4
10.92-12.45 [.430-.490]	BLACK	552007-1	552006-1	552008-1
CABLE RANGE DIAMETER		COLOR	GROOVE SIDE PART NO.	TONGUE SIDE PART NO.
				KIT PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

DWN
D. STRAUSSER
CHK
M. HUGHES
APVD
M. HUGHES

16APR97
21APR97
21APR97

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

COVER KIT, 180 DEGREE,
50 POSITION, CHAMP

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-552008

RESTRICTED TO
-

SCALE
2:1

SHEET
1 OF 1

REV
U