

Zack marker strip - ZB 8/27 - 0807216


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 8.2 mm, Lettering field: 10.5 x 8.15 mm

The illustration shows versions ZB 8 - UNPRINTED, -LGS:CONSEC.NOS, -QR:CONSEC.NOS and CUS

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 157975
Weight per Piece (excluding packing)	2.95 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	27 mm
Width (a)	8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

Zack marker strip - ZB 8/27 - 0807216

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - BLUEMARK MAG ZB 8/27 - 5146558

Magazine for BLUEMARK, only for ZB 8/27 UV-100 - 0829102