

Clip, 10.3 x 38 mm, UR



20 A (UL)



**Description**

- Through hole mounting

**Standards**

- UL 4248-1 / UL 512

**Approvals**

- UL File Number: E41738

**Applications**

- Combiner Boxes in Photovoltaic Systems

**References**

Fuseholder to [ASO 10.3x38](#)

**Weblinks**


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

**Technical Data**

Fuse-Link	10.3 x 38 mm
Mounting	PCB
Terminal	Solder THT
Rated current	20A (UL)
Degree of Protection	IP 00
Material: Terminals	see variants
Unit Weight	4.1 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	Type, Approvals

Soldering Methods	Wave
Solderability	235 °C / 2 sec acc. to IEC 60068-2-20, Test Ta, method 1
Resistance to Soldering Heat	260 °C / 10 sec acc. to IEC 60068-2-20, Test Tb, method 1A
Contact Resistance	< mΩ at 20 mV

**Dimension**



Drilling diagram

**All Variants**

Clip	Terminal	Material: Terminals	Order Number
●	Straight	Tin-Plated Bronze	7170.0470

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

**Packaging Unit** Bulk (50 pcs.)