


© 1969 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

UNPUBLISHED COPY NOT TO BE REPRODUCED NOR PUBLISHED WITHOUT WRITTEN PERMISSION OF AMP INCORPORATED.



TONGUE MATERIAL THK. = .031
FOR "C"/"D" WIRE INS DIA

TABLE II

9-52273-1	WHITE	18	.056 .110	18	---
8-52273-1	RED	20	.046 .110	20	
7-52273-1	GREEN	22	.038 .110	22	
52273-2	WHITE	18	.056 .110	18	
52273-1	RED	20	.046 .110	20	OBS. 52273-5
52273	GREEN	22	.038 .110	22	OBS. 52273-3
PART NO.	COLOR CODE	WIRE SIZE	"C"/"D"	WIRE STAMPING	PART NO. ON TAPE

REVISIONS				
ZONE	DATE	DESCRIPTION	DATE	APPROVED
O	9-12-69	NPS 69-0454, 0455 & 0456	LE	FCY
A	12-18-69	REVISED PC-5569	LE	FCY
B	1-5-70	REVISED B-630	SH	FCY
C	1-19-70	ADDED TAPE NO. 52273-3	LE	FCY
D	6-15-70	ADDED TAPE NO. 52273-4	WM	FCY
E	10-28-70	ADDED TAPE NO. 52273-5	RY	Qme
F	5-3-76	ADDED .062 MIN. COLOR BAND-67322-4	6-3-76	5-3-76
G	3-19-80	REV. PER PC-B592	12B	19M
H	12/22/80	REV. PER PC-8820	dc	19M
J	12-17-82	INACTIVATED -3 PER P-9273	PMF	19M
K	10-9-87	OBSOLETE REV. G 2588	BT	PMF
L	3-16-93	REV./ 0720-0043-93	TO	ML
M	11/DEC/00	REV PER 063A-0801-00		DR/TM

TABLE I

100	LOOSE PC, BOX	9-52273-1	SEE TABLE II	BODY: COPPER (QQ-C-576) TIN PL (MIL-T-10727) SLEEVE: COPPER (QQ-C-576) TIN PL (MIL-T-10727) INSULATION: NYLON (MIL-M-20693) TYPE I, COLOR: RED	
100	LOOSE PC, BOX	8-52273-1			
100	LOOSE PC, BOX	7-52273-1			
1	WIRE TERMINAL INSULATION RESTRICTING				
QTY.	DESCRIPTION	PART NO.	MATERIAL & FINISH		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON DECIMALS: .008 ANGLES: 5°		CONTRACT NO. —#—	AMP INCORPORATED HARRISBURG, PENNSYLVANIA		
MATERIAL		DR. <i>G. Epler</i> 9-11-69	WIRE TERMINAL PIDG-RING TONGUE INSULATION, RESTRICTING		
SEE TABLE I		CHK. <i>P.C. [unclear]</i> 9-12-69			
		APPR. <i>Swabell</i> 9-15-69			
		<i>PM Esmeringer</i> 9-24-69			
		DATE APPR. _____	SIZE B	CODE IDENT. NO. 00779	NUMBER 52273
		OTHER APPR. _____	SCALE NTS	SHEET 1 OF 1	

CUSTOMER DRAWING