

Geocel® ALL WEATHER MATE

ALL WEATHER SEALANT

Geocel® All Weather Mate sealant is a single component, high performance elastomeric all weather sealant that adheres to most wet or damp surfaces making it ideal for emergency repairs and remedial sealing. Suitable for sealing treated and untreated timber, brick, concrete, plastic, most metals, stone, glass and asphaltic materials.

- Excellent adhesion to most common construction substrates
- One component, easy to apply and tool
- Suitable for use on damp and wet surfaces
- Cures to form a flexible seal with high movement capability
- Mildew resistant
- High gloss finish
- Can be overpainted

SPECIFICATIONS

Manufactured under ISO 9001



TECHNICAL DATA

Storage Life	12 months from date of manufacture when stored in temperatures below 30°C
Colour	White, Clear
Tack Free Time	72 hours
Cure Rate	5 days (6mm bead)
Specific Gravity	0.95
Tensile Strength	2.0Mpa
Elongation	800%
Service Temperature	-40°C to +80°C

Specification writers: These values are not intended for use in preparing specifications. Please contact your local **Geocel® Sales Representative** prior to writing specifications on this product.

APPLICATION

Ensure gaps and cracks to be filled are free from dust, dirt and grease. Remove nozzle and cut off end of cartridge. Replace nozzle and cut the tip to the required width. Place the cartridge in a cartridge gun and apply material into gap and crack to be filled. Ensure **Geocel® All Weather Mate** makes full contact with the sides and back of the joint.

FINISHING

When applied to wet surfaces tooling is necessary to ensure that a good bond with the surface is formed. Always tool down immediately following application using a spatula or a piece of wood wetted with a dilute soap solution.

CLEAN UP

Excess sealant may be cleaned off whilst in an uncured state using a dry disposable cloth. Alcohol based solvents can be used to clean tools.

PAINTING

Geocel® All Weather Mate sealant may be painted after 24 hours, some paints may crack in dynamic joints. Please see paint manufacturer's specifications.

LIMITATIONS

Geocel® All Weather Mate is not suitable for surfaces that bleed oils or plasticisers. It should be ensured that the sealant is compatible with the substrates to which it is being applied.

PACKAGING

Geocel® All Weather Mate is supplied in 310ml cartridges packed in boxes of 12.

HEALTH AND SAFETY

Health and Safety data sheets available on request.

TECHNICAL SERVICE

For further technical information, advice on suitability for specific applications, or detailed Health and Safety information, contact **Geocel® Technical Service**.

IMPORTANT NOTE The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that Geocel's products are safe, effective and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

Geocel's sole warranty is that the product will meet the Geocel sales specifications in effect at the time of shipment.

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.

Geocel specifically disclaims any other express or implied warranty of fitness for a particular purpose or merchantability.

Geocel disclaims liability for any incidental or consequential damage.

Geocel®

Geocel Limited

Western Wood Way, Langage Science Park, Plympton, Plymouth, Devon, PL7 5BG

Tel: 01752 334350 Fax: 01752 202065 Email: info@geocel.co.uk

www.geocel.co.uk