

Datasheet

RS Pro Non-Fused Terminal Block, 12 Way/Pole, Screw Down Terminals, 16 mm², PP, 400 V

RS Stock No: **703-3820**



Product Details

RS Pro non-fused terminal block is made from polypropylene. This material has many qualities, some of which include are lightweight and rigidity, corrosion resistant and high tensile strength. This terminal block is coloured white, with the screw down terminals raised to aid wiring to the brass contacts. The terminal block with 12 ways, has a pitch size of 15 mm. This terminal block with 16-mm² wire, has a voltage rating of 400 V.

Features and Benefits

- High tensile strength
- Easy wiring installation
- Recessed housing for safety
- Meets CE (BS EN 60998) standards



ENGLISH

Specifications:

Contact Material	Brass
Current Rating	30 to 76 A
Material	Polypropylene Housing
Maximum Operating Temperature	+85°C
Number of Ways	12
Pitch	15 mm
Termination Method	Screw Down
Voltage Rating	400 V
Wire Size	16 mm ²
Colour	White
Dimensions	165 x 25.5 x 19.8 mm
Standards Met	RoHS, CE (BS EN 60998)